
IMP E A Touchless XT Mains Operated



Touchless Euro dispenser with pump front removal for soaps and disinfectants
Art.-No. 4400901

OPHARDT HYGIENE-TECHNIK GmbH + Co. KG Lindenau 27 | 47611 Issum | Germany Tel.: +49 (0) 28 35 18-10 | Fax +49 (0) 28 35 18-77 planer@ophardt.com | www.ophardt.com

IMP Touchless XT







References

hospitals, clinics, retirement/care homes, dental practices, fitness and sports centres, restaurants, commercial kitchen, industry, conference centres, laboratories, food processing areas, rehabilitation facilities, rescue stations, administration facilities

Usage examples

Passage area, entrance area, Intensive care units, dialysis stations, surgery areas, nursing and examination rooms, clean room, therapy rooms

3

Technical data

Dispenser type: Euro bottle dispenser

Housing: Aluminium, matte silver anodized

Face shield: Plastic, white Filling volume (ml): 500 ml

Dosing pump: long-life stainless steel pump with bent suction tube

Dosage quantity: 0.75 / 1.0 / 1.2 / 1.5 ml/stroke Filling good: Disinfectant, Liquid soaps, Lotion

Operating type: Touchless, Touchless, with extendable emergency lever

Power type: Mains operated

Batteries: 5x Alkaline D batteries, 1.5 V, exchangeable, non-rechargeable

Recommended Batteries: DURACELL ULTRA POWER D, VARTA 4020 (INDUSTRIAL), VARTA 4120, VARTA 4720

Wall bracket: Standard ingo-man® plastic wall plate
Mounting: Wall mounting with 3 screws and wall plugs

Cleaning: manual wipe disinfection

Warranty: 5 years Dimensions (W x H x D) in mm: 94x295x209

Hinweis: Before using new products, please always check the compatibility of the product and the dispensing system to ensure

proper functionality.

Compatible accessories

SH 4 IMP Touchless
Prevents disinfectant from dripping off hands and onto the floor

Art.-No. 1416600

SH 5 IMP Touchless

Prevents disinfectant from dripping off hands and onto the floor

Art.-No. 1418684

Please see other accessories in our Online Product Catalogue.